

DryDome®

DryDome is a compact dryer from the makers of Dry & Store®.

Gentle convection heat removes damaging moisture from hearing instruments of all types. A subtle LED indicator glows for the 8-hour cycle.

Everyday use is recommended for best results.

Features

Instant Activation: Easy-to-use 1 touch interface

High Evaporative Rate: 0.25 grams per hour


Best-in-Class 2 Year Warranty

Automatic off after 8 hours

No need to remove batteries—just open battery door


Accommodates 2 hearing aids or 1 implant processor

Customize DryDome with your logo printed here!



Physical Properties	
Weight	2.5 oz. (70.87 gm)
Unit size	3.45" (8.76 cm) diameter
Drying compartment	single tray 2.25" (5.7 cm) diameter

Electrical Characteristics	
Conforms to IEC 60950-1 Ed. 2.0, CISPR 14-1, Ed. 5.1: 2009, CISPR 14-2, Ed. 1.2: 2008	
Input	100-240 Volts AC, 50/60 Hz, 1 Amp
Output	5 volts DC, 1.0 Amp Max. Micro USB connector
Power supplies used with this product are certified to one or more of the following:	UL, CE, ETL, CSA, GS, PSE/JET, C-Tick, KC, and SABS. Consult label on power supply for certifications.
Operating Temperature	Up to 113°F (45°C) when using manufacturer's power supply



EAR TECHNOLOGY CORPORATION
Helping people hear better, every day.

info@eartech.com | 1-800-327-8547 | eartech.com

P.O. BOX 1516, JOHNSON CITY, TN 37605 USA

©ETC DD SPC 0216