

Product Overview

Dry & Store® Professional

Dry & Store® Global II

Zephyr by Dry & Store®

The Dry & Store® family offers you three options for unparalleled drying of all types of hearing aids, cochlear implant hardware, and other hearing instruments such as ear monitors and noise maskers.



Shown above: the sleek new Global II, the Professional and the Zephyr.

Dry & Store® Global II



- Utilizes Dry-Max™ technology
- Automatic one-button operation
- UV lamp kills 99% of common bacteria found in the external ear canal, significantly reducing itching, irritation and infection.
- Works with either the Dry-Brik® desiccant or a rechargeable can-type desiccant
- Compact and portable, only 1 lb., 3 oz. (.5 kg) 7.2" wide x 4.9" deep x 3.3" high (18.3 cm x 12.4 cm x 8.4 cm)
- Single drying compartment accommodates up to two ear-level cochlear implant processors or four behind-the-ear hearing aids or one body-worn processor
- The AC adapter with the Global II can be used anywhere in the world—no voltage converter necessary. All that's needed is the appropriate plug adapter, or you can travel "adapter-free" by ordering individual power supplies with native plugs. (Choose from US, UK, Europe, Australia or South African plugs.)
- Distributed worldwide. Ships with a universal switching power supply and plug appropriate for the purchaser's country of origin.
- Will also work with an inverter for 12V service
- One year manufacturer's warranty; made in Thailand

— MSRP \$107.95 —

Dry & Store® Professional



- Utilizes Dry-Max™ technology
- Automatic one-button operation
- UV lamp kills 99% of common bacteria found in the external ear canal, significantly reducing itching, irritation and infection.
- Uses the Dry-Brik® desiccant only
- 9" wide x 7" deep x 6" high, 2 lb., 8 oz. (1.1 kg) (Suitable for home use; not designed for travel)
- Partitioned drying compartment keeps two sets of hearing aids separate (helpful for families with more than one hearing aid user)
- Accommodates up to four in-the-ear or behind-the-ear hearing aids or two cochlear implant ear-level processors
- Ergonomic design provides ease of use for persons with arthritis, stiff joints, or other dexterity limitations due to the easy-open drawer and smooth, curved interior
- 120VAC service, for distribution in North America only
- Two year manufacturer's warranty; made in America

— MSRP \$164.95 —

Zephyr by Dry & Store®



- Utilizes Dry-Max™ technology
- Automatic one-button operation
- Works with either the Dry-Brik® desiccant or a rechargeable can-type desiccant
- Ideal for travel, only 13.4 oz. (.4 kg) 3.6" wide x 5.9" deep x 2.8" high (9.1 cm x 15 cm x 7.1 cm)
- Single drying compartment accommodates one cochlear implant (BWP or BTE) or two behind-the-ear hearing aids or one body-worn processor
- The AC adapter with the Zephyr can be used anywhere in the world—no voltage converter necessary. All that's needed is the appropriate plug adapter, or you can travel "adapter-free" by ordering individual power supplies with native plugs. (Choose from US, UK, Europe, Australia, or South African plugs.)
- Distributed worldwide. Ships with a universal switching power supply with plug appropriate for the purchaser's country of origin
- Will also work with an inverter for 12V service
- One year manufacturer's warranty; made in Thailand

— MSRP \$78.95 —

All three models feature Dry-Max™, the most effective combination of technologies available anywhere for the drying of encased micro-electronic devices.

EAR TECHNOLOGY CORPORATION

For more information call 1.800.327.8547 or e-mail info@dryandstore.com
www.dryandstore.com